


# WORK AREA | QuickPort® Surface-Mount Boxes & Back Boxes

**COPPER**

work area



## QUICKPORT SURFACE-MOUNT BOXES & BACK BOXES

- Surface-mount boxes and back boxes work in places where it may not be practical to add a wallbox
- Boxes mount with the included double-sided tape or screws, modular furniture brackets (page A24), or with magnets
- Surface-mount boxes and back boxes have breakouts to match common surface-mount raceway systems
- 4S089 products are designed to work with Leviton shielded or eXtreme® CAT 6A connectors to allow proper bend radius control

QUICKPORT SURFACE-MOUNT BOXES				
DESCRIPTION	WHITE	IVORY	GREY	BLACK
<b>[A]</b> 12-Port Surface-Mount Box, 7.60"W x 5.02"D x 1.13"H	41089-12W	41089-12I	41089-12G	41089-12E
<b>[B]</b> 6-Port Surface-Mount Box, 6.38"W x 3.22"D x 1.08"H	41089-6WP	41089-6IP	41089-6GP	41089-6EP
<b>[C]</b> 4-Port Surface-Mount Box, 4.77"W x 3.21"D x 1.05"H	41089-4WP	41089-4IP	41089-4GP	41089-4EP
<b>[D]</b> 2-Port Surface-Mount Box, 2.52"W x 2.22"D x 1.10"H	41089-2WP	41089-2IP	41089-2GP	41089-2EP
<b>[E]</b> 1-Port Surface-Mount Box, 1.42"W x 2.22"D x 1.10"H	41089-1WP	41089-1IP	41089-1GP	41089-1EP
<b>[F]</b> 2-Port Surface-Mount Box for Shielded Connectors, 2.5"W x 3.00"D x 1.22"H	4S089-2WP	4S089-2IP		
<b>[G]</b> 4-Port Surface-Mount Box for Shielded Connectors, 5.6"W x 5.20"D x 1.22"H	4S089-4WP	4S089-4IP		
SINGLE AND DUAL-GANG SURFACE-MOUNT BACK BOXES				
DESCRIPTION	WHITE	IVORY	GREY	BLACK
<b>[H]</b> Single-Gang Standard Back Box, 4.72"H x 2.96"W x 1.89"D	42777-1WA	42777-1IA	42777-1GA	42777-1EA
<b>[I]</b> Single-Gang Shallow Back Box, 4.72"H x 2.96"W x 1.45"D	42777-1WB	42777-1IB	42777-1GB	42777-1EB
<b>[J]</b> Dual-Gang Standard Back Box, 4.72"H x 4.77"W x 1.89"D	42777-2WA	42777-2IA	42777-2GA	42777-2EA
<b>[K]</b> Dual-Gang Shallow Back Box, 4.72"H x 4.77"W x 1.45"D	42777-2WB	42777-2IB	42777-2GB	42777-2EB
MAGNETS				
DESCRIPTION				PART NO.
<b>[L]</b> Set of 4 Magnets, 1.00"H x 0.84"W x 0.30"D				41030-SMJ

See color swatches on page A24.

Use one magnet for 2-port surface-mount housing. Use two magnets for 4-, 6-, and 12-port surface-mount housings and single- and dual-gang surface-mount back boxes.